




Desk and Clamp Lamp

User Guide



The Preferred LED Desk Lamp

Congratulations on the purchase of your Bright Reach® Lamp! We know you will quickly come to love all that this lamp has to offer!

1


Get to Know Your Lamp

Control Panel:

- ⓘ To turn the lamp ON or OFF
- Ⓜ To change light color
- ⊕ To brighten the light
- ⊖ To dim the light



Control Panel



Remote Control :

- ⓘ To turn the lamp ON or OFF
- Ⓜ To change light color
- ⊕ To brighten the light
- ⊖ To dim the light




2

Instructions to Change Base:

Your lamp is a desk and a clamp lamp! A 2-in-1 design. We have made it easy for you to move from room-to-room.

Your lamp comes mounted on the desk base. If you wish to change to the clamp base:

- 1) Untighten the 2 screws on backside of control panel. Be sure to not untighten too far so that they come out of the threads. This way the screws won't be separated from the base.
- 2) Hold base with one hand, and control panel of lamp with the other hand and slide lamp to the right.
- 3) Insert lamp into clamp base by sliding to the left. Tighten the 2 screws to hold lamp in place (NOTE: make sure "FRONT" printed on bottom of lamp points towards you.)
- 4) Reverse steps to change back to desk base.




3

Instructions For Use:

1. Connect to Power

Connect the power adapter to the input on side of the lamp control panel, and connect plug to wall outlet. The cord is magnetic for ease of use and longevity of the port. (Please note that slight sparking is normal upon connection)

NOTE: ① Make slow adjustments to Base Arm swivel. Fast movements can cause the magnetic plug to become detached.
② Be sure the power cord is not laying at an angle. It should run straight back towards the wall socket/rear of lamp.




2. Operating the Lamp

Touch Sensitive Control Panel

- Quick touch ⓘ to turn the light ON/OFF.
- Quick touch Ⓜ to change light color: 6 options
- Quick touch ⊕ to brighten the light: 20%-40%-60%-80%-100%
- Quick touch ⊖ to dim the light: 100%-80%-60%-40%-20%

6 Light Color Options!

warm+	warm-	neutral-	neutral+	cool-	cool+
3000K	3400K	3800K	4400K	4800K	5200K



3. Advanced Operation

Advanced Control Panel Settings:

- Touch and hold Ⓜ to turn off yellow backlight LEDs.
- Touch and hold ⊕ or ⊖ for stepless dimming.


NOTE: Remote operates in the same manner as touchpad controls.

4


4. Exact Light Positioning

NOTE: When adjusting your Bright Reach® lamp, make sure to firmly hold the base to lessen the pressure of movement to the arms.


- Light Bar Arm can be adjusted 200 degrees up/down.
- Base Arm can be adjusted 125 degrees up/down.



- Light Bar Arm can be adjusted 135 degrees left/right with our patented glare control hinge. Swivel the Light Bar Arm left and right to find the perfect position for you.




- Entire lamp can be adjusted 135 degrees left/right by turning on the base. Hold the Base Arm to swivel.




5

- USB port built in for charging other devices (DC5V 1000mA)



- Fold flat and unplug for storage. A great space saving option!



Moving Rooms or Leaving the House?

Make your lamp portable with our durable battery pack and integrated holder. Call us today or order online.

5. Remote control holder: If you would like to use the remote with the holder included, tear off the adhesive square and adhere it on the remote control holder, then adhere the holder on the lamp Base Arm in your desired position. (back of Base Arm recommended.) This is an optional step.

Warnings:

- To avoid electric shock, **do not** disassemble in any way.
- At brightest setting light bar can become hot to the touch- use caution and adjust properly. Silicone sleeve is meant for heat dissipation. **Removal is not recommended.**
- Use only original manufacturer parts and adapters.
- Do not overextend the hinges, overextending can cause damage to the lamp.
- Do not use or place the lamp in high-temperature or high-humidity environments. Indoor use only
- Do not look at the LED light source directly, doing so can cause damage to your eyes.

6

- In case of any malfunction, **IMMEDIATELY** disconnect the power cord and **DISCONTINUE USE**. Call for further instructions.
Examples of possible malfunction:
 - The power cord or power plug breaks or is loose
 - The lamp becomes damp or wet
 - The lamp hinge breaks
 - The light bulb or surrounding area starts to smoke or spark
 - Abnormal flickering
- If lamp arm(s) become loose or do(es) not hold position, the hinge(s) can be tightened. To accomplish this at home:
 - 1) Isolate the hinge that is not holding the desired position
 - 2) Locate two small silver or black discs on each side of the hinge. On one side of the hinge, either right or left, there is a nut that needs to be tightened.
 - 3) Remove the disc with a flat edged device, ie: optical sized flathead screwdriver, or the like. (NOTE: do not use a sharp edged device, as you may cut yourself)
 - 4) Tighten the nut with needle nose pliers until the nut becomes tight.
 - 5) Re-adhere the disc back over the hinge hole with existing adhesive (NOTE: replacement discs are available - please call)
 - 6) If these instructions fail, we have socket kits available to send to you if needed. Please call us.

IMPORTANT: WHEN ADJUSTING THE LAMP, MAKE ADJUSTMENTS SLOWLY AND CAREFULLY ACCORDING TO INSTRUCTIONS. Rough handling and over-bending or overextending hinges can cause damage to the lamp.

Cleaning Instructions:

- Unplug your lamp prior to cleaning.
- Dampen a cloth (moist, not dripping) or use a disinfecting wipe to clean the metal portions of the lamp and control panel.
- Do not use a damp cloth or a disinfecting wipe on the LED light bar diffuser - only use a dry, soft cloth to clean.

7

Specifications:

Brightness	2500 lumens, 11,000 lux @11"
Dimming	5 steps or stepless
Color Accuracy	85+ CRI
LED Lifespan	50,000 hours
Light Color CCT	3000K 3400K 3800K 4400K 4800K 5200K
Power	AC: 110-240V 50/60Hz; DC: 12V/2.5A
Energy Usage	26 watts
Annual Energy Cost	\$6.55 (.23 cents Kwh average based on 3 hours/day)
Patent	US D925,104 S
Material	Steel and Aluminum
Warranty	2 years against manufacturer defects
Color	Silver/Black
Qty of LED	120pcs
Battery	Battery pack available (not included)
Remote	Included - takes 2 "AAA" batteries

Certifications



Bright Reach® Lamps

a Division of Mattingly Low Vision, Inc.

El Paso, Texas

+1.915.201.1669 OR info@brightreachlamps.com

Item#LAMPBRD (Black or Silver)

Designed in Texas

Made in China

www.brightreachlamps.com



8